

SPK

Data sheet - rev. 1.0


Spherical Plain Bearings - Tesno

Self-lubricating spherical-plain bearings with PTFE, series K, DIN ISO 12240-1, maintenance free.

FEATURES AND ADVANTAGES

- Outer ring: C45 (1.1191) carbon steel and PTFE bonded on the inner surface
- Inner ring: tempered, ground and polished steel for bearings 100Cr6 (1.3505)
- Maintenance: maintenance free
- Temperature range: -40° C to +200° C
- USE & MAINTENANCE : [see this page](#)
- STATIC LOAD SERVICE LIFE : [see this page](#)
- TOLERANCES : [see this page](#)

COMPONENTS AND DIMENSIONS



Type	Measurements [mm]								Tilt angle	Rotational speed limit	Axial factor		Basic load rating		Radial clearance	Weight
	d	D	d1	B	C	dk	rs	r1s	α (°)	n _{max} (min ⁻¹)	Y	Y0	dyn C (kN)	stat C0 (kN)	CN (μm)	kg
SPK5	5	13	7.7	8	6	11.1	0.3	0.3	13	-	-	-	8.3	14.9	20-50	0.01
SPK6	6	16	8.9	9	6.75	12.7	0.3	0.3	13	-	-	-	11	19.6	20-50	0.01
SPK8	8	19	10.4	12	9	15.6	0.3	0.3	14	-	-	-	19	34.1	20-50	0.02
SPK10	10	22	12.9	14	10.5	19.1	0.3	0.3	13	-	-	-	27.1	48.6	20-50	0.03
SPK12	12	26	15.4	16	12	22.22	0.3	0.3	13	-	-	-	36.7	65.7	20-50	0.04
SPK14	14	28	16.8	19	13.5	25.4	0.3	0.3	15	-	-	-	47.6	85.3	20-50	0.09
SPK16	16	32	19.3	21	15	28.6	0.3	0.3	15	-	-	-	60	107.4	20-50	0.1
SPK18	18	35	21.8	23	16.5	31.7	0.3	0.3	15	-	-	-	73.8	132.2	20-50	0.13
SPK20	20	40	24.3	25	18	34.9	0.3	0.6	14	-	-	-	89	159.5	20-50	0.15
SPK22	22	42	25.8	28	20	38.1	0.3	0.6	15	-	-	-	108.6	194.4	20-50	0.21
SPK25	25	47	29.5	31	22	42.8	0.3	0.6	15	-	-	-	135	241.7	20-50	0.3
SPK30	30	55	34.8	37	25	50.8	0.3	0.3	17	-	-	-	182.9	327.5	20-50	0.36
SPK35	35	62	37.7	43	28	57.2	0.6	1	19	-	-	-	231.5	414.5	20-50	0.49
SPK40	40	75	44.2	49	35	66.6	0.6	1	16	-	-	-	319.7	572.4	20-50	0.9
SPK50	50	90	55.8	60	45	82.5	0.6	1	14	-	-	-	544.5	975	20-50	1.6

ROTATIONAL UNITS