

DGE ES-2RS

Data sheet - rev. 1.0

Spherical Plain Bearings - Basic Line


Spherical-plain bearing sliding combination steel / steel, with -2RS lip seals on both sides, series E, according to DIN ISO 12240-1

FEATURES AND ADVANTAGES

- Outer ring: ball bearing steel, hardened, ground, phosphated, single split, with oil groove and drill holes, with -2RS lip seals on both sides
- Joint ball: ball bearing steel, hardened, ground, phosphated
- Maintenance: maintenance required, oiled on delivery, initial lubrication by the user
- Temperature range: -40° C to +120° C
- USE & MAINTENANCE : [see this page](#)
- STATIC LOAD SERVICE LIFE : [see this page](#)
- TOLERANCES : [see this page](#)



COMPONENTS AND DIMENSIONS



Type	Measurements [mm]								Tilt angle	Rotational speed limit	Axial factor		Basic load rating		Radial clearance	Weight
	d	D	d1	B	C	dk	rs	rs1	α (°)	n_{max} (min ⁻¹)	Y	Y0	dyn C (kN)	stat C0 (kN)	CN (µm)	kg
DGE 15 ES-2RS	15	26	18	12	9	22	0.3	0.3	8	-	-	-	17	85	40-82	0.03
DGE 16 ES-2RS	16	30	19	14	10	25	0.3	0.3	10	-	-	-	21.2	106	40-82	0.04
DGE 17 ES-2RS	17	30	20	14	10	25	0.3	0.3	10	-	-	-	21.2	106	40-82	0.04
DGE 20 ES-2RS	20	35	24	16	12	29	0.6	0.3	9	-	-	-	30	146	40-82	0.06
DGE 25 ES-2RS	25	42	29	20	16	35.5	0.6	0.6	7	-	-	-	48	240	50-100	0.11
DGE 30 ES-2RS	30	47	34	22	18	40.7	0.6	0.6	6	-	-	-	62	310	50-100	0.14
DGE 35 ES-2RS	35	55	39	25	20	47	0.6	1	6	-	-	-	80	400	50-100	0.22
DGE 40 ES-2RS	40	62	45	28	22	53	0.6	1	7	-	-	-	100	500	60-120	0.3
DGE 45 ES-2RS	45	68	50	32	25	60	0.6	1	7	-	-	-	127	640	60-120	0.4
DGE 50 ES-2RS	50	75	55	35	28	66	1	1	6	-	-	-	156	780	60-120	0.54
DGE 60 ES-2RS	60	90	66	44	36	80	1	1	6	-	-	-	200	1220	60-120	1
DGE 70 ES-2RS	70	105	77	49	40	92	1	1	6	-	-	-	315	1560	72-142	1.5
DGE 80 ES-2RS	80	120	88	55	45	105	1	1	6	-	-	-	400	2000	72-142	2.2
DGE 90 ES-2RS	90	130	98	60	50	115	1	1	5	-	-	-	490	2450	72-142	2.7
DGE 100 ES-2RS	100	150	109	70	55	130	1	1	6	-	-	-	610	3050	85-165	4.3
DGE 110 ES-2RS	110	160	121	70	55	140	1	1	6	-	-	-	655	3250	85-165	4.7
DGE 120 ES-2RS	120	180	135	85	70	160	1	1	6	-	-	-	950	4750	85-165	8
DGE 140 ES-2RS	140	210	155	90	70	180	1	1	7	-	-	-	1080	5400	85-165	11
DGE 160 ES-2RS	160	230	170	105	80	200	1	1	8	-	-	-	1360	6800	100-192	14
DGE 180 ES-2RS	180	260	199	105	80	225	1.1	1.1	6	-	-	-	1530	7650	100-192	18.5
DGE 200 ES-2RS	200	290	213	130	100	250	1.1	1.1	7	-	-	-	2120	10600	100-192	28
DGE 220 ES-2RS	220	320	239	135	100	275	1.1	1.1	8	-	-	-	2320	11600	100-192	35.51
DGE 240 ES-2RS	240	340	265	140	100	300	1.1	1.1	8	-	-	-	2550	12700	100-192	39.91
DGE 260 ES-2RS	260	370	288	150	110	325	1.1	1.1	7	-	-	-	3030	15190	110-214	51.54
DGE 280 ES-2RS	280	400	313	155	120	350	1.1	1.1	6	-	-	-	3570	17850	110-214	65.06
DGE 300 ES-2RS	300	430	336	165	120	375	1.1	1.1	7	-	-	-	3800	19100	110-214	78.07
DGE 320 ES-2RS	320	440	344.6	160	135	380	1.1	3	4	-	-	-	4361	21803	125-239	77
DGE 340 ES-2RS	340	460	366.6	160	135	400	1.1	3	3.8	-	-	-	4590	22950	125-239	82
DGE 360 ES-2RS	360	480	388.3	160	135	420	1.1	3	3.6	-	-	-	4820	24098	135-261	84.2
DGE 380 ES-2RS	380	520	407.9	190	160	450	1.5	4	4.1	-	-	-	6120	30600	135-261	129

